



Pharma Screen

SALIENT FEATURES

Customized Solutions



- Adequate material Inlet
- Inspection Window for Operation Monitoring
- Can be provided with CIP ball spray

Leak tight screen fitting



- · Perfectly locating of screen to avoid any leakage
- Less material retention on screen
- · Provided with quick openable toggle clamp

Super tight screen



- Super tight wire mesh fitted on sturdy frame.
- Silicon molding on border and specially developed silicon gasket on fitting edge.
- No welding, No lead soldering, No crevices.

Excellence in fabrication



- · No joints in bottom discharge cane
- · Joint less dome helps in equal material distribution over area
- · Easy washdown

Lockable / Movable Caster Wheels



- · Lockable / Movable Caster wheels for free movement of equipment.
- · Wheels molded from polyirethane.

Motion Generator



- · Perfectly designed Motion Generator, sturdy, robust construction Silent in operation.
- · Oversized roller bearings for longer life and to sustain heavy vibrations.

Unbalanced Weight



- · Geometry of unbalanced weight gives excellent tilting effect to the material on screen
- Different flow patterns of materials can be generated by changing relative positions of unbalanced weights.

Minimal screen blinding



- · Minimum screen blinding because of super tightness of screen fixing and tilting effect generated by motion generator
- · Life of screen increases drastically than ordinary screens available in market

No sharp Corners



- · All welded joints perfectly finished, ground and polished to 220 Grit.
- Special motor guard for safety and protection
- Specially developed spring locators for dampening

Marketed by:



HINDUSTAN **VIBROTECH** (((((====:)))))

For more details please contact:

Corporate Office

2, Vrindavan, Subhash Road, Vile Parle (E) Mumbai - 400 057 Maharashtra, INDIA

: +(91)-(22)-26838937 Tel. **Telefax:** +(91)-(22)-66929928 E-Mail: hindvibro@gmail.com response@kampanind.com

Visit us at : www.kampanind.com